



H2 PURITY METER

Online mains Operated for Mixture of two Gases (Non-Corrosive)
Single pass

Range: 0 to 100% Resolution 0.1% (For H₂ /N₂ – H₂ in N₂) - (balance gas N₂)
(Calibration gas required near sample gas) l,

- TCD Filament (imported) Diffusion type.
- One needle valve and Rota meter for Gas Flow Control.
- Inlet / outlet 1/8 “

Electronic Control Panel:

- Digital Display 3 1/2 LED with 0.1% resolution.
- 230 Volt AC
- Zero & Span (**or two points**) control for calibration to get direct read out of H₂ Purity
- Adjustable single Alarm. (Potential free Relay Contact.)
- 4 to 20 mA online operation
- Cabinet – table mount or panel mount. (**Panel Cutout: 235 x 138mm**)

Calibration : - By sample reference selector valve for calibration
Purpose. To be calibrated with standard calibration gas.

♦ **In the interest of continued product upgrade we reserve the right to change the specification without prior notice**

Hemaki
LAB-SERVICES

252-D Amar Gian Industrial Estate, L..B.S. Marg, Khopat, Thane (W) 400 6
Maharashtra, India Tel. +91 (022) 2547 49 01 Telefax : 2547 58 68
Email : hemaki@vsnl.com Web site : www.hemaki.com